


WCPES-Series WaterClear™ Polyethersulfone

WCPES-Series High Purity WaterClear™ Polyethersulfone Filter Cartridges are a value-oriented choice for cost effective, general purpose membrane filtration. Designed in continuous lengths up to 30" for excellent performance value. The highly retentive polyethersulfone membrane offers excellent flux density and low protein-binding. The naturally hydrophilic membrane wets easily to allow for the maximum utilization of the surface area. These features allow the WCPES-Series to provide the fine performance of PES membrane at a competitive price. Designed to tolerate repeated hot water sanitization and in-situ steam sterilization cycles. Manufactured in a clean-room environment to maintain high standards of purity and cleanliness.

Flow Rate vs Pressure Drop



Typical Applications

- Deionized Water Systems
- General-Use Water Filtration
- Liquid Clarification
- Chemical Filtration

Ordering Information

WCPES	Rating (μ)	A	Length	C	End Cap Style	O-Rings/Gaskets	-	Adders
	0.04		10" (25.4 cm)		2= DOE Flat Gasket	B = Buna		I = Stainless Steel Insert ²
	0.1		20" (50.8 cm)		3= 222 w/ Fin	E = EPDM		R = 18 Megaohm Rinse ³
	0.2		30" (76.2 cm)		4 = 222 w/ Flat Cap	S = Silicone		HP = Heavy Poly Core
	0.45		40" (101.6 cm) ²		6 = 226 w/ Flat Cap	T = FEP FKM (if O-ring and PTFE if DOE)		
	0.65				7 = 226 w/ Fin			
	0.8				16 = 213 Internal O-Ring ¹	V = FKM		
					28 = 222 3-tabs w/ Fin	Z = FEP Silicone		

¹ Silicone and EPDM only

² Stainless Steel Insert (I) Adder comes standard with the Heavy Poly Core (HP)

³ Made in the USA.

DISCLAIMER: Filtration data presented is representative of performance observed in controlled laboratory testing. It is not given as a warranty, specification or statement of fitness for use. Specific performance can vary widely depending on contaminant type, fluid properties, flow rates and environmental conditions. It is recommended that users conduct thorough qualification testing to assure the product functions as required. For additional technical support, a product Performance Guide is available upon request.

DS_WCPES_D009C-EN



Construction Materials

Membrane.....Polyethersulfone
Support Media.....Polypropylene & PE/PET
End Caps.....Polypropylene
Center Core.....Polypropylene
Outer Support Cage.....Polypropylene
O-Rings/Gaskets.....Buna, EPDM, Silicone, PTFE, FEP Silicone, FEP FKM, FKM

Sanitization / Sterilization

Filtered Hot Water.....80°C for 30 min.
Steam Sterilization.....121°C for 30 min., multiple cycles

Chemicals: Cartridges are compatible with most chemical sanitizing agents.

Note: Stainless steel insert option required for all cartridges being hot water sanitized or steam sterilized for 222 or 226 endcaps.

Dimensions

Length:
 10 to 40 inches (25.4 to 101.6 cm) nominal
Outside Diameter:
 7.0 cm nominal

Operating Conditions

Change Out ΔP (recommended).....2.4 bar
Temperature (max).....80°C
Differential Pressure (max).....3.4 bar at 20°C

Toxicity

All polypropylene components meet the specifications for biological safety per USP Class VI – 121°C for plastics.

FDA Listed Materials

Materials of construction comply with FDA regulations for food and beverage contact use as detailed in the US Code of Federal Regulations, 21CFR. Materials used to produce filter media and hardware are deemed safe for use in contact with foodstuffs in accordance with EU Directives 1935/2004 and/or 10/2011.